




CD207FK

Fitting Kit

Dynamic Strut *made of Resilergy™*

Weight Range depends on flex - Light to Medium Activity Level



CD207XS - Extra Soft Flex Kit
Weight Range 70-150 lbs.

CD207S - Soft Flex Kit
Weight Range 90-200 lbs.

CD207M - Medium Flex Kit
Weight Range 125-225 lbs.

CD207R - Rigid Flex Kit
Weight Range 200-280 lbs.

CD207XR - Extra Rigid Flex Kit
Weight Range 260-350 lbs.

6-month warranty against manufacturer defects, excessive wear or breakage.
External Prosthetic Components



CD207FK_post.revA.03242025


















Manufactured by Coyote®
419 N. Curtis Rd., Boise, Idaho 83706 USA
(208) 429-0026 | www.coyote.us



Advana Limited
Tower Business Centre
2nd Flr, Tower Street
Swatar, BKR 4013
Malta

Fitting Kit Box for the Dynamic Strut AFO - Map & Parts Included

<p>XSoft, Soft, Medium Top - 6x20 (4) Bottom - 6x22 (4)</p> 	<p>Dynamic Strut Demos for Fitting - CD207XSS, CD207SS, CD207MS,</p> 			
<p>Rigid & Extra Rigid Top - 6x22 (4) Bottom - 6x25 (4)</p> 	<p>Dynamic Strut Demos for Fitting - CD207RS, CD207XRS</p> 			
<p>Black Screws 6x14 (8) For XS, S 6x16 (8) For M, R, XR</p> 	<p>AFO Tooling Piece (4)</p> 	<p>AFO Upper Mounting Plate (1)</p> 	<p>AFO Lower Mounting Plate (1)</p> 	<p>AFO Plate Foam (4)</p> 
<p>Countersunk Washers (4)</p> 	<p>Shim Button Head Screws XSoft, Soft, Medium 6x20, 6x25 (2 each)</p> 	<p>Shim Button Head Screws Rigid & Extra Rigid 6x22, 6x30 (2 each)</p> 	<p>Shim Self Leveling Washers Washer Bottom (4) Top (4)</p> 	<p>Rotation Shim (2)</p> 
				<p>Flexion Shim (2)</p> 

See instructions online.

www.coyote.us/instructions-dynamicstrut

EN | Instructions for Use
 DE | Gebrauchsanweisung
 FR | Notice d'utilisation
 ES | Instrucciones para el uso
 IT | Istruzioni per l'uso
 NO | Bruksanvisning
 DA | Brugsanvisning

SV | Bruksanvisning
 EL | Οδηγίες Χρήσης
 NL | Gebruiksaanwijzing
 PT | Instruções de Utilização
 PL | Instrukcja użytkowania
 TR | Kullanım Talimatları
 RU | Инструкции по использованию

JA | 取扱説明書
 ZH | 中文说明书
 KO | 사용 설명서
 CS | Návod k použití
 FI | Käyttöohjeet

