



Zero Clearance Locks *Coyote*

www.coyote.us/proximal

Ordering Tree



CD116

Proximal Lock

Comes with fabrication tooling.
Silicone glue included with lock.

CD101

Summit Lock

Mounted externally with rivet after fabrication. Controls rotation.

CD102

Summit Low-Pro Lock

Comes with fabrication tooling.



CD108 | Integrator™
(2 3/8" diameter)



CD108S | Small Integrator™
(2" diameter)

Connectors



CD103AF

Alignable Connector

Offset up to .6"

Thermoforming and Lamination



CD111

One-Shot Connector

Offset up to .6"

Lamination only



CD115CF5

5 Degree AK Connector

Capable of up to 1.5" of Offset with 5 degrees of flexion angle.

Alignment



CD103SDI

Single Direction Insert

Offset up to .33"



CD103MDI

Multi-Direction Insert

Offset up to .33"



Quik Glue

For custom Offset

Offset up to .6"

Adjust anatomically with the limb through offset alignment capability and can be adjusted vargus, valgus, extension, or flexion.

Additions

Wave Suction Band

5 Sizes

Silicone adhesive included



The Summit liner attachment is applied with "Coyote Quik Glue" or a 5 minute epoxy.

Only use silicone based adhesive with Proximal Lock attachment.

